760 - 830 nm

830 - 920 nm

920 - 1100 nm

1100 - 1300 nm

1300 - 1450 nm

1450 - 1650 nm

1650 - 1850 nm

1850 - 1900 nm

1900 - 2200 nm

2200 - 2600 nm

2600 - 3000 nm

3000 - 6000 nm

# DFB laser diodes from 2600 nm to 3000 nm



# nanoplus single mode laser diodes

nanoplus is the only manufacturer world-wide routinely providing single and multi mode lasers at any wavelength from 760 to 6000 nm. At wavelengths up to 14  $\mu$ m, QCLs complete nanoplus' laser portfolio. Our patented distributed feedback laser diodes deliver single mode emission with well defined optical properties enabling a wide range of applications.

nanoplus lasers operate reliably in tens of thousands of installations worldwide, including chemical and metallurgical industries, gas pipelines, power plants, medical systems, airborne and satellite applications.

# key features

- √ very high spectral purity
- ✓ narrow linewidth
- √ excellent reliability
- √ wide variety of packaging options
- ✓ customer-specific designs available

## application areas

- √ high performance gas sensing for process and environmental control
- √ precision metrology
- √ atomic clocks
- √ spectroscopy
- √ space technology

nanoplus lasers with excellent performance are specifically designed and characterized to fit your needs. This data sheet summarizes typical properties of nanoplus DFB lasers in the range from 2600 nm to 3000 nm. In this wavelength regime e. g.  $H_2O$ , HF,  $CO_2$  can be detected with particularly high sensitivity, since the detection sensitivity typically increases at long wavelengths. Overleaf data for DFB lasers optimized for  $H_2O$  detection is shown as an example.

general ratings (T = 25 °C)	symbol	unit	typical
optical output power	P <sub>out</sub>	mW	2
reverse voltage	$V_{r}$	V	1.8
forward current	I <sub>f</sub>	mA	100
side mode suppression ratio (SMSR)		dB	> 32

On request, lasers with specifically optimized properties, e. g. higher output power, are available.

# laser packaging options

TO5.6 header with or without cap

TO5 with TEC and NTC

For dimensions and accessories, please see www.nanoplus.com Further packaging options available

Further pactopations availing on request.

device protected by US patent 6.671.306 US patent 6.846.689 EU patent EP0984535

> phone: +49 (0) 931 90827-0 fax: +49 (0) 931 90827-19 email: sales@nanoplus.com internet: www.nanoplus.com





ISO

9001:



# nanoplus DFB laser diodes at 2740 nm


A wide variety of gas molecules exhibit characteristic absorption lines in the near infrared. DFB lasers emitting at 2740 nm are perfectly suited for highly sensitive detection of small  $H_2O$  concentrations. For this application, highly stable laterally and longitudinally single mode lasers are required.


This data sheet reports performance data of nanoplus DFB lasers at this wavelength. Similar performance data are obtained in the entire wavelength range from 2600 nm to 3000 nm. For examples of performance data of nanoplus lasers in other wavelength ranges, please see www.nanoplus.com or contact sales@nanoplus.com

Fig. 1 Room temperature cw spectrum of a nanoplus DFB laser diode operating at 2740 nm

In many applications, temperature and / or current variations are used to adjust the laser emission precisely to the target wavelength.

Fig. 2 Mode hop free tuning of a nanoplus 2740 nm DFB laser diode by current variation at different temperatures





electrooptical characteristics (T = 25 °C)	symbol	unit	min	typ	max
peak wavelength	λ	nm	2739	2740	2741
threshold current	I <sub>th</sub>	mA	30	50	80
slope efficiency	е	mW/mA	0.05	0.08	0.12
temperature tuning coefficient	C <sub>T</sub>	nm/K	0.15	0.20	0.27
current tuning coefficient	Cı	nm/mA	0.01	0.02	0.03
slow axis (FWHM)		degrees	20	30	40
fast axis (FWHM)		degrees	40	50	60
emitting area	WxH	μт х μт	3 x 1	4.5 x 1.5	5 x 2
storage temperatures	T <sub>s</sub>	°C	- 40	+ 20	+ 80
operational temperature at case	T <sub>c</sub>	°C	- 20	+ 25	+ 50

We will be happy to answer further questions. Please contact us at sales@nanoplus.com



nanoplus Nanosystems and Technologies GmbH Oberer Kirschberg 4 D-97218 Gerbrunn phone: +49 (0) 931 90827-0 fax: +49 (0) 931 90827-19 email: sales@nanoplus.com internet: www.nanoplus.com © copyright nanoplus GmbH 2013, all rights reserved. nanoplus GmbH reserves the right to modify these specifications at any time without notice and is not liable for errors.

